

8LS1-4PG

[Products](#) > [Switches](#) > [Limit Switches](#) > [General Purpose Limit Switches](#) > [LS Series](#) > **8LS1-4PG**

Overview

MICRO SWITCH LS Series General Purpose Limit Switches, Wobble - Flexible Cable, 1NC 1NO DPDT Snap Action, Double Break, PG13,5 conduit, Compact/Non Plug-in, ...
[View More](#)



Technical Specifications

Availability	Global	Operating Force (OF)	1,39 N [5 oz] max.
Pretravel (PT)	28,6 mm [1.125 in] max.	Product Type	MICRO SWITCH Compact Limit Switches
Actuator	Wobble - Flexible Cable	Termination Type	PG13,5
Circuitry	1NC 1NO SPDT Snap Action, Double Break	Supply Voltage	120 Vac, 240 Vac, 480 Vac/115 Vdc/230 Vdc/550 Vdc
Housing Material	Zinc Die-Cast	Ampere Rating	10 A Ind./0.8 A Res./0.4 Res./0.1 A Res.

[View More](#)

View documents in: English

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
MICRO SWITCH LS Series General Purpose Limit Switches	Datasheet	English	5MB
PK 81028: LS Limit Switches	Installation Instructions	English	397KB
PK 81241: Gold contact LS	Installation Instructions	English	16KB
MICRO SWITCH Limit Switches Comparison	Product Range Guide	English	460KB

[View More](#)

Product Features

- Mode of operation is field adjustable
- NEMA 1, 3, 4, 6, and 13
- Wide choice of heads and actuators
- Variety of operating characteristics

view all 8LS1-4PG literature

view distributor inventory

sample request

email support

get support

email sales

find a distributor

email this page

- Captive screws
- UL and CSA approved parts available

Applications

- Machine tools
- Conveyors
- Material handling
- Metal fabrication equipment
- Lift trucks

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

TERMS & CONDITIONS

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.