







RECOMMENDED P.C.B. LAYOUT



CIRCUIT: SPST
CONTACT CONFIGURATION

NOTES:

- 1. ALL DIMENSIONS IN MM
- 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- 3. RATING: 50mA, 12VDC
- 4. CONTACT MATERIAL: Silver
- 5. TRAVEL: 0.25 +0.2/0.1mm
- 6. OPERATING FORCE: 160±50gf
- 7. CONTACT RESISTANCE: 100mILLI-Ohms Max
- 8. 2002/95/EC (ROHS) COMPLIANT



OBJECT ID: 000017751

E-SWITCH®

D	15281	REV. DESCRIPTION, ROHS NOTE	9/14/05	PH
C	11324	REVISED PART DESCRIPTION	7/20/01	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

TITLE TL1240NQ				
SCALE 4:1	DATE 7/30/01	DR CJB	DWG P010330	REV D