



with self-tapping thread – steel

Choose version

steel 11SMnPb30, galvanized with undercut

▼

 **Download information as pdf**

☐ **Show technical details**

Order number	Hexagonal size (SW)	External thread (G1)	Internal thread (G2)	Standard lengths in mm (L)	Amount	Order
222ST2.2 x (length)	SW5	ST2.2	M2.5	Please select ▼	100	Please log in 
224ST2.9 x	SW5.5	ST2.9	M3	Please select ▼	100	Please log in 
224ST3.3 x	SW5.5	ST3.3	M3	Please select ▼	100	Please log in 
225ST3.5 x	SW6	ST3.5	M3	Please select ▼	100	Please log in 
226ST4.2 x	SW7	ST4.2	M4	Please select ▼	100	Please log in 
228ST4.8 x	SW8	ST4.8	M5	Please select ▼	100	Please log in 
229ST6.3 x	SW10	ST6.3	M6	Please select ▼	100	Please log in 

Order example: 222ST2.2 × 15oF = DIA / steel / SW5 / M2.5 - ST2.2 × 15oF

Tolerance for length dimensions: + / - 0.1 mm