

**Part Number :** [797582024](#)

**Product Description :** Pre-Crimped Lead KK 254  
Female-to-KK 254 Female, Tin (Sn) Plating, 300.00mm  
Length, 24 AWG, Black

**Series Number :** 79758

**Status :** Active

**Product Category :** Power and Signal Cable  
Assemblies



---

## Documents and Resources

### Drawings

[797582024\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |                                                |
|--------------------|------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                   |
| China RoHS         | per SJ/T 11365-2006                            |
| EU ELV             | Not Relevant                                   |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21             |
| REACH SVHC         | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS            | Compliant per EU 2015/863                      |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

Part Details

General

|                        |                                                                                                   |
|------------------------|---------------------------------------------------------------------------------------------------|
| Status                 | Active                                                                                            |
| Category               | Power and Signal Cable Assemblies                                                                 |
| Series                 | 79758                                                                                             |
| Description            | Pre-Crimped Lead KK 254 Female-to-KK 254 Female, Tin (Sn) Plating, 300.00mm Length, 24 AWG, Black |
| Assembly Configuration | Pre-crimped Lead Only                                                                             |
| Connector to Connector | KK Cat Ear Crimp Terminals                                                                        |
| Keyword                | Pre-Crimped Leads                                                                                 |
| Product Name           | KK                                                                                                |
| UPC                    | 889056822770                                                                                      |

Physical

|                                |                      |
|--------------------------------|----------------------|
| Cable Length                   | 300.00mm             |
| Circuits (Loaded)              | 1                    |
| Circuits (maximum)             | 1                    |
| Color - Resin                  | Black                |
| Gender                         | Female-Female        |
| Material - Metal               | Brass                |
| Material - Plating Mating      | Tin                  |
| Material - Plating Termination | Tin                  |
| Net Weight                     | 1.321/g              |
| Packaging Type                 | Bag                  |
| Plating min - Mating           | 1.016µm              |
| Single Ended                   | No                   |
| Termination Interface Style    | Crimp or Compression |
| Wire/Cable Type                | UL 1007              |
| Wire Size (AWG)                | 24                   |