



Part Number : [1301280115](#)

Product Description : Woodhead FD Gray Glass-Filled Polyester Box, (2) 19.05mm (.750") Threaded Knock-out Openings

Series Number : 130128

Status : Obsolete

Product Category : Power Distribution

Engineering Part Number : 453

Documents and Resources

Drawings

[1301280115 sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Power Distribution
Series	130128
Description	Woodhead FD Gray Glass-Filled Polyester Box, (2) 19.05mm (.750") Threaded Knock-out Openings
Enclosure Rating	N/A
NEMA Configuration	N/A
Product Name	Woodhead
Type	FD Box - Industrial Duty
UPC	78678872453

Agency

CSA	LR32159
UL	E117594

Electrical

Current - Maximum per Contact	N/A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	N/A

Physical

Cord Diameter	N/A
Cord Grip Body Size	N/A
Cord Length	N/A
Cord Type	N/A
Feed-Thru	Yes
Flip Lid	No

Material - Housing	PBT Glass-Filled
Mounting Style	Permanent
Number of Receptacles	0
Packaging Type	Carton
Receptacle Type	N/A

This document was generated on May 23, 2026

Obsolete