






THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	RoHS Compliancy	06-01-06	DP
C	Graphics Update	03-20-08	DP



CONTROLLED

NOTES:

MATERIAL:

HOUSING: THERMOPLASTIC
TERMINAL: COPPER ALLOY

RATING:

UL, CSA: 15A 250V AC
VDE: 10A 250V AC

INSULATION RESISTANCE: OVER 100 OHM 500V DC

DIELECTRIC STRENGTH: 2000V AC ONE MINUTE

APPROVALS: UL, CSA, VDE

RoHS COMPLIANT

2	Soldering PIN Brass Strip t=0.8mm Tin-Plated	3
1	Body Insulator PBT Black Color	1
Qualtek Electronics Corp.		
PPC DIVISION		
Part Number: 710W-00/02		RoHS Compliant
Description: AC RECEPTACLE		
Dim range (mm)	Tolerance +/- (mm)	
0-1	0.15	
1-6	0.20	
6-18	0.30	
18-50	0.50	
50-120	0.70	
120-250	0.90	
250-500	1.20	
UNIT: mm		REV.C
Drawn / Date		Checked / Date
B. ZHANG 04-12-02		Approved / Date
		JJH / 04-12-02