


## PLASTIC HOODS

## MHDSSK-T/P-SERIES

### TECHNICAL SPECIFICATIONS

|                               |                                                  |
|-------------------------------|--------------------------------------------------|
| <b>Material:</b>              | Polyamid UL-recognised                           |
| <b>Operating Temperature:</b> | -55°C to +110°C                                  |
| <b>Cable Entry:</b>           | Side and Top<br>Side Only<br>Top Only            |
| <b>Thumbscrews:</b>           | UNC 4-40 (standard)<br>M2,5 or M3,0 upon request |
| <b>Cable Diameter:</b>        | Up to 11,5 mm                                    |
| <b>Colour:</b>                | Black                                            |
| <b>Accessories:</b>           | See page 120                                     |
| <b>Assembly Instruction:</b>  | See page 145                                     |



| Size DSSK-T/P | Dim A | Dim B | Dim B |
|---------------|-------|-------|-------|
| 9-way         | 31,5  | 40,0  | 43,0* |
| 15-way        | 40,0  | 40,0  | -     |
| 25-way        | 53,5  | 43,0  | -     |
| 37-way        | 71,3  | 40,0  | -     |

\* Top only

### Features:

- Available in sizes 9-15-25-37
- Suitable for any common Sub-D connector
- Quick-snap locking system
- Re-openable
- Company logo available upon request
- Also available in Metalized Version, See page 13

L = Side + Top Entry  
S = Side Entry  
T = Top Entry

### Ordering information:

| Size:  | P/N - Kitted: | Product Code:   | L |
|--------|---------------|-----------------|---|
| 9-way  | 6260-0107-01  | MHDSSK-P-09-L-K |   |
| 15-way | 6260-0107-02  | MHDSSK-P-15-L-K |   |
| 25-way | 6260-0107-03  | MHDSSK-P-25-L-K |   |

| Size:  | P/N - BULK:  | Product Code: | L |
|--------|--------------|---------------|---|
| 9-way  | 6261-0107-01 | MHDSSK-P-09-L |   |
| 15-way | 6261-0107-02 | MHDSSK-P-15-L |   |
| 25-way | 6261-0107-03 | MHDSSK-P-25-L |   |

| Size:  | P/N - Kitted: | Product Code:   | S |
|--------|---------------|-----------------|---|
| 9-way  | 6260-0107-11  | MHDSSK-P-09-S-K |   |
| 15-way | 6260-0107-12  | MHDSSK-P-15-S-K |   |
| 25-way | 6260-0107-13  | MHDSSK-P-25-S-K |   |
| 37-way | 6260-0107-14  | MHDSSK-P-37-S-K |   |

| Size:  | P/N - BULK:  | Product Code: | S |
|--------|--------------|---------------|---|
| 9-way  | 6261-0107-11 | MHDSSK-P-09-S |   |
| 15-way | 6261-0107-12 | MHDSSK-P-15-S |   |
| 25-way | 6261-0107-13 | MHDSSK-P-25-S |   |
| 37-way | 6261-0107-14 | MHDSSK-P-37-S |   |

| Size:  | P/N - Kitted: | Product Code:   | T |
|--------|---------------|-----------------|---|
| 9-way  | 6260-0107-21  | MHDSSK-P-09-T-K |   |
| 15-way | 6260-0107-22  | MHDSSK-P-15-T-K |   |
| 25-way | 6260-0107-23  | MHDSSK-P-25-T-K |   |

| Size:  | P/N - BULK:  | Product Code: | T |
|--------|--------------|---------------|---|
| 9-way  | 6261-0107-21 | MHDSSK-P-09-T |   |
| 15-way | 6261-0107-22 | MHDSSK-P-15-T |   |
| 25-way | 6261-0107-23 | MHDSSK-P-25-T |   |

