










HARDWARE:



LOCKING WASHER




O-RING



SWITCH FUNCTION

Model No.	POS. 1	POS. 2
DPW 1 BG	ON	(OFF)
Term. Conn.	1-3	OPEN

PANEL CUT-OUT



Compliance: RohS III (2015/863/EU)

Tolerances: 0.00: ±0.25mm 0.0: ±0.40mm			Date 02/14	Name dr	DPW 1 BG D2P x		
					knitter-switch		
Accessory	10/19	dr	30 30 34			Page	
Modifications	Date	Name				1/2	

Specifications:

Contact rating:

Contact resistance:

Insulation resistance:

Dielectric strength:

Operating temperature:

Mechanical life:

Electrical life:

Operating force:

Soldering conditions:

Panel thickness:

Travel:

Torque:

Material:

IP rating:

max.: 500mA, 48V AC; 200mA, 50V DC; 200mA, 250V AC

50mOhm max.

1GOhm min. at 500V DC

1500V AC RMS

-30°C to +85°C

1 000 000 cycles

500 000 cycles

2-5N

350°C max., 5sec.

1.5mm min. - 4.0mm max.

1.5mm

1.5Nm max. applied to nut

Case: diallyl phthalate (DAP) (UL94V-0)

Cap: polyamide 6/6

Terminal / contacts: gold over silver plated

Bushing: zinc alloy, black ED-coated

IP 67 (mounted)

x	Cap colour
W	white
K	black
R	red
O	orange
Y	yellow
G	green
B	blue

Compliance: RohS III (2015/863/EU)

Tolerances: 0.00: ±0.25mm 0.0: ±0.40mm			Date	Name	DPW 1 BG D2P x				
			02/14	dr					
			knitter-switch			30 30 34			Page
Accessory	10/19	dr							2/2
Modifications	Date	Name							