



Rev	AWO #	Description	Date	Appr
-		RELEASED	12/2/19	


APPROVED: _____

DATE: _____ TITLE: _____


TITLE: _____




SECTION A-A




SECTION B-B




SECTION C-C



Reel package direction: As below shown.



Direction



Crimping side upper
Strip carrier on top.

SPECIFICATIONS:

Material:

Terminal: 0.30MM Thickness, Brass, Tin plated

Mechanical:

Wire Range: #18~20 AWG

Insulator O.D: 2.80~2.55MM

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

APPROVALS		DATE
DRAWN	OW	12/2/19
CHECKED	AC	12/2/19
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE	FEMALE CRIMP FOR DDF SERIES TIN PLATED, ON REELS
-------	---

SIZE X	PART NO. DFC-01D-R	REV -
REF: S00119T	SCALE: NTS	SHEET 1 OF 1