




LAYOUT DIMENSIONS (after plating)



TIN LEAD PART NUMBER

DC21WA4P500A30

DC21WA4P500A40

PART NUMBER

LEAD FREE PART NUMBER

DC21WA4P500A30LF


DC21WA4P500A40LF

PART NUMBER

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:	
SEE DRAWING C01-8639-0001	

European Views

rev	ecn no	dr	date
B	-	DEB	2003/10/01
C	LS05-001	MPE	2005/03/09
D	LS06-0095	LGO	2006/06/28
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JARRY	2001/01/24	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 1.5		
Eng	PESSON	2001/01/24			0.XX	±0.1				
Chr	LEGARE	2001/01/24			0.XX ±2	0.XXX		±0.1		
Appr	LEGARE	2001/01/24	Product family				D-SUB	Spec ref -		
			PINS CONNECTORS RIGHT ANGLED				dwg no C01-8639-1845	Rev.		
			WITH POWERS CONTACTS					D		
catalog no			-				CUSTOMER	sheet	of	