






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C190323	2019/03/04	Vicky	Change Note




Recommended Panel
Cut-Out





AAD-XXPMMS-LC7001

02:2Pin
03:3Pin



△ Note:

- * Ⓞ Important Dimension To Check.
- * Waterproof Rate: IP67, Unmated.
- * Housing: Thermoplastic, Black.
- * Pin: Copper Alloy, Gold Plated.
- * Nut: Thermoplastic, Black.
- * Gasket: Rubber, Gray.
- * Use with waterproof cap or dust cap
Maximum Panel Thickness: 2.3mm
- * Use without waterproof cap or dust cap
Maximum Panel Thickness: 3.5mm
- * Gasket and Nut are packed separately in PE bags.
(Gasket/Nut不組裝, 散裝出貨)



3 Pin 2 Pin
Pin Assignments Front View

UNIT:mm		TOLERANCE		TITLE		Amphenol LTW		ITEM NO		DRAWN BY		DATE	
.X ±0.25		.XX ±0.1		SCALE 2:1		安費諾亮泰企業股份有限公司		DWG NO		Vicky		2019-03-04	
.XXX ±0.05		ANGLES ±1°		SIZE A4				AAD-XXPMMS-LC7001		CHECKED BY		DATE	
REV. B		WC-REV. A.3		SHEET 1 OF 1				CUSTOMER		Rita		2019-03-04	
				QC: Inspection item				ALTW		APPROVED BY		DATE	
										Max		2019-03-04	