



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE3-710144	2006/12/13	Gao Ling	Move O-ring to ZSE00100840
C	LEN1380073	2013/08/02	Sam	Modify Dimension




Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate : IP68
IP68: 1M of depth of water 24 hours
(防水等級: IP68)
(IP68: 1米水深 24 小時)
- * Do Mating Test After Glued
點膠後, 須作對插測試
- * Add glue can't highly exceed pin
(點膠高度不得蓋過 pin 針)
- * DVI Conn. : Black Core, Nylon66
- * Plastic Jacket : Black, Nylon+GF
- * Pin : Copper Alloy, Gold Plated
- * Ring : Light Blue, Silicone
- * Screw : Copper Alloy, Nickel Plated, #4-40 UNC



Screw L=5.0 For Panel Thickness
Under 1.2mm
適用板厚為 1.2mm 以下

Screw L=6.0 For Panel Thickness
Between 1.2~2.0mm
適用板厚為 1.2~2.0mm



Recommended Panel Cut-Out
建議挖孔尺寸

UNIT: mm	TITLE
TOLERANCE .X ± 0.25 .XX ± 0.1 .XXX ± 0.05 ANGLES $\pm 1^\circ$	Female DVI Connector(24+1)
SCALE 1:1	SIZE A4
REV. C	WC-REV. A.6
	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO.	DRAWN BY	DATE
DDD-25PFFS-SL8001	SamChang	2013-08-02
DWG NO.	CHECKED BY	DATE
DDD-25PFFS-SL8001	Rita	2013-08-02
CUSTOMER	APPROVED BY	DATE
ALTW	Maslow	2013-08-02