


Data Sheet | Item Number: 216-288

Ferrule; Sleeve for 6 mm² / AWG 10; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; yellow

<https://www.wago.com/216-288>



Color: ■ yellow

Similar to illustration

Dimensions in mm

Connection Data		
Metric cross-section of the ferrule		6 mm ²
Strip length		20 ... 21 mm / 0.79 ... 0.83 inches
Cross-section (AWG) of ferrule		10 AWG

Physical data		
Total length (L)		26 mm
Wall thickness of crimp sleeve (W2)		0.2 mm
Wall thickness (plastic collar W1)		0.3 mm
Crimp length (length of sleeve L1)		18 mm
Inner diameter of plastic collar (D1)		6.3 mm
Diameter crimp sleeve inside (D2)		3.5 mm

Mechanical data		
Plastic collar		Standard collar
Suitable		2010 to 2016 Series

Material data		
Color		yellow
Fire load		0.016 MJ
Weight		0.5 g



Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	100 pcs
Packaging type	Bag
Country of origin	DE
GTIN	4055143654760
Customs tariff number	85369010000

Product Classification	
UNSPSC	39121405
eCl@ss 10.0	27-40-02-01
eCl@ss 9.0	27-40-02-01
ETIM 9.0	EC000005
ETIM 10.0	EC000005
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 216-288

↓

Documentation			
Bid Text			
216-288	11.09.2017	doc 24.50 KB	↓
216-288	19.02.2019	xml 2.80 KB	↓

CAD/CAE-Data


CAD data

2D/3D Models 216-288

↓



Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable