




Ordering Code:

CU02 S A H 0 000
① ② ③ ④ ⑤ ⑥


- ① Series No.
② S= Socket
③ Plating option:
A= Selective Gold flash
plated over 1.27μm(50 μin) Nickel
C= Selective 0.76μm(30 μin) Gold plated
over 1.27μm(50 μin) Nickel
④ H= Right angle
⑤ Insulator Color: 1= Black, 0= White
⑥ Option: 000= Standard

Materials :




Insulator: Glass filled polyester UL 94V-0

Contacts: Phosphor Bronze

Shell: Brass With Nickel plated



Recommended P.C. Board Layout



Lead Free Process

RoHS Compliant

⑦	Karen	1/09-20'	ECNT120010/ECRD119041	CIVILUX 2020.01.16 ISSUED			DATE	UNIT: mm / inch		TITLE: U.S.B TYPE B RIGHT ANGLE BOARD MOUNT SOCKET		 瀚荃股份有限公司 CviLux Corporation					
⑥	Sun	11/26/07'	ECR07090-1/ECN07486		DRAWN BY:	Karen	1/9-20'	TOLERANCE UNLESS OTHERWISE SPECIFIED								MATERIAL:	
⑤	Sandy	3/28-07'	ECN07109		ENGINEER:	Sun	1/13-20'			.X ± 0.25/.010	X' ± 4'						
④	Sandy	1/16/06'	ECN06495/ECR06080-1		CHECKED BY:	Eisley	1/14-20'	.XX ± 0.20/.008	X' ± 2'	FINISH:							
SYM	NAME	DATE	REVISIONS		APPROVED BY:	Eisley	1/14-20'	.XXX ± 0.10/.004	.XX ±								
												DRAWING NO.	CU0202SP	PART NO.	CU02S*H*000		
												SCALE	3 / 1	SHEET	1 OF 1		