

216RS4

Wall mounted socket

2CMA193097R1000



Wall mounted socket, earthing sleeve position 4h, rated current 16A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Yellow

GENERAL

Product Name	Wall mounted socket
Product ID	2CMA193097R1000
Function	Wall mounted socket
EAN	739269699
Catalog Description	Surface socket-outlet, 4h, 16A, IP44, 2P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420031
E-Number Norway	1542301
E-Number Sweden	E2416442
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	ERS
Color	Yellow
Number of Poles	3
Clock Position	4Hour
Rated Current	16 ampere
Rated Voltage	100 ... 130 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	66 millimetre
Product Net Height	91 millimetre
Product Net Length	117 millimetre
Product Net Depth	117 millimetre
Product Net Weight	0.22 kilogram

PACKAGING

Package Width	138 millimetre
Package Height	345 millimetre
Package Gross Weight	2.2 kilogram
Package Length	158 millimetre
Package Units	box 10 piece