

DISCONNECT & TEST

SCREW TERMINAL BLOCKS

HIGHLIGHTS

FEATURES

- Slider Style Disconnect Terminals
- **CDTTU** - Standard Slider Disconnect
- **CDTTU-SH** - Double Disconnect Terminal
- **CDTTUFT** - Same profile Feed-Through
- Specially designed socket headed screws act as fast monitoring points
- Disconnect is achieved by operating sliding link with screw driver

APPLICATIONS


- Disconnect & Test Applications

SLIDER STYLE DISCONNECT TERMINAL BLOCKS

CDTTU



CDTTU-SH



CDTTUFT



Dimensions & Weight

Width	
Length	
Height w DIN Rail	35 x 7.5 mm 35 x 15 mm
Weight per piece	

Slider Disconnect Terminal	
8 mm	
63 mm	
58.7 mm 65.7 mm	
28.5 g	

Slider Double Disconnect Terminal	
16 mm	
63 mm	
58.7 mm 65.7 mm	
59.2 g	

Feed Through Terminal Slider Disconnect Profile	
8 mm	
63 mm	
58.7 mm 65.7 mm	
27.1 g	

Technical Data/Ratings

Approvals	CE, ENEC, TUV SUD, TUV Rheinland
Wire Size (solid / stranded)	
Voltage Rating	
Current Rating	
Torque	
Insulation Material	Polyamide 66

UL E220514, C-SP US, IEC 60947-7-1	
16-8 AWG, 1.5-10 mm ²	
600 V, 800 V	
41 A, 57 A	
14 lb-in, 1.2 Nm	
Polyamide 66	

UL E220514, C-SP US, IEC 60947-7-1	
16-8 AWG, 1.5-10 mm ²	
300 V, 300 V, 160 V	
25 A, 25 A, 10 A	
14 lb-in, 14 lb-in, 1.2 Nm	
Polyamide 66	

UL E220514, C-SP US, IEC 60947-7-1	
16-8 AWG, 1.5-10 mm ²	
600 V, 800 V	
41 A, 57 A	
14 lb-in, 1.2 Nm	
Polyamide 66	

Installation Instructions

Wire Stripping Length	12 mm
Screwdriver	Flat Head 1.0 x 5.5 mm

12 mm	
Flat Head 1.0 x 5.5 mm	

12 mm	
Flat Head 1.0 x 5.5 mm	

12 mm	
Flat Head 1.0 x 5.5 mm	

Terminal Blocks

Grey (standard)	
Red R	
Blue BU	
Black BL	
Orange O	
Green G	
Yellow Y	
White W	

Cat. No.	Std. Pk.
CDTTU	50
CDTTU/R	50
CDTTU/BU	50
CDTTU/BL	50
CDTTU/O	50
CDTTU/G	50
CDTTU/Y	50
CDTTU/W	50

Cat. No.	Std. Pk.
CDTTU-SH	20
CDTTU-SH/R	20
CDTTU-SH/BU	20
CDTTU-SH/BL	20
CDTTU-SH/O	20
CDTTU-SH/G	20
CDTTU-SH/Y	20
CDTTU-SH/W	20

Cat. No.	Std. Pk.
CDTTUFT	50
CDTTUFT/R	50
CDTTUFT/BU	50
CDTTUFT/BL	50
CDTTUFT/O	50
CDTTUFT/G	50
CDTTUFT/Y	50
CDTTUFT/W	50

Accessories

End Plate	
DIN Rail	32mm, 35mm
End Stop	
Shorting Plug	2 pole
External Jumper	2 pole, 3 pole, 4 pole, 10 pole
Shorting Plug	
Marking Tag	

Cat. No.	Std. Pk.
EPCDTTU	50
2511120	20
CA701-15/S	20
2511160	10
CA702	50
CA802	50
CA202	25
QJ8/2	25
CA710/2	100
CA710/3	50
CA710/4	50
CA710/10	20
QJ8/2	25
MT8	1 Pk. (100 tags)

Cat. No.	Std. Pk.
EPCDTTU	50
2511120	20
CA701-15/S	20
2511160	10
CA702	50
CA802	50
CA202	25
QJ8/2	25
CA710/2	100
CA710/3	50
CA710/4	50
CA710/10	20
QJ8/2	25
MT8	1 Pk. (100 tags)

Cat. No.	Std. Pk.
EPCDTTU	50
2511120	20
CA701-15/S	20
2511160	10
CA702	50
CA802	50
CA202	25
QJ8/2	25
CA710/2	100
CA710/3	50
CA710/4	50
CA710/10	20
QJ8/2	25
MT8	1 Pk. (100 tags)