

Part number

# CCMA 2.5



Male crimp contact, CC series, 16 A, turned silver plated, wire cross section 2,5 mm<sup>2</sup>, AWG 14

## Product description

|                     |               |
|---------------------|---------------|
| <b>Product type</b> | Crimp contact |
| <b>Series</b>       | CC            |
| <b>Gender</b>       | Male          |

## Technical data

|                           |                      |
|---------------------------|----------------------|
| <b>Current</b>            | 16 A                 |
| <b>Wire cross-section</b> | 2,50 mm <sup>2</sup> |
| <b>AWG size</b>           | 14                   |
| <b>Contact type</b>       | Turned silver plated |

## Further technical details

|                                    |        |
|------------------------------------|--------|
| <b>Weight</b>                      | 1,40 g |
| <b>Conductors stripping length</b> | 7,5 mm |

## Material properties

|                              |                                                                                |
|------------------------------|--------------------------------------------------------------------------------|
| <b>Main material</b>         | Copper alloy                                                                   |
| <b>RoHs conformity</b>       | Compliant with exemption 6(c): copper alloy containing up to 4% lead by weight |
| <b>China RoHs - EFUP</b>     | 50                                                                             |
| <b>REACH SVHC substances</b> | Yes<br>Lead                                                                    |
| <b>SCIP number</b>           | C0979fba-9907-458f-a94a-db781440f273                                           |

## Approvals / Standards

|                       |          |
|-----------------------|----------|
| <b>Certifications</b> | CSA, EAC |
| <b>UL</b>             | ECBT2    |

## General ordering information

|                   |               |
|-------------------|---------------|
| <b>EAN13 code</b> | 8015747012393 |
| <b>eCl@ss 8.1</b> | 27440204      |
| <b>ETIM 7.0</b>   | EC000796      |

## Packaging Information

|                                  |                      |
|----------------------------------|----------------------|
| <b>Packaging length</b>          | 112,00 mm            |
| <b>Packaging height</b>          | 95,00 mm             |
| <b>Packaging width</b>           | 117,00 mm            |
| <b>Packaging weight</b>          | 1,27 kg              |
| <b>Packaging volume</b>          | 1,24 dm <sup>3</sup> |
| <b>Packaging description</b>     | Carton box           |
| <b>Packaging quantity</b>        | 800 Pcs              |
| <b>Packaging EAN code</b>        | 8015747103923        |
| <b>Sub-packaging length</b>      | 50,00 mm             |
| <b>Sub-packaging height</b>      | 44,00 mm             |
| <b>Sub-packaging width</b>       | 50,00 mm             |
| <b>Sub-packaging weight</b>      | 0,16 kg              |
| <b>Sub-packaging volume</b>      | 0,11 dm <sup>3</sup> |
| <b>Sub-packaging description</b> | Plastic box          |
| <b>Sub-packaging quantity</b>    | 100 Pcs              |
| <b>Sub-packaging EAN barcode</b> | 8015747012409        |

Part number



# CCMA 2.5

Catalogue drawings



---

## Notes

Dimensions shown in mm are not binding and may be changed without notice.

