


[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)

[Home](#) / [Products](#) / [X-Lok](#) / [Standard Size](#)

Product Line

[Single Pair Ethernet](#) >[ZConnect](#) >[Ceres](#) >[X-Lok](#) >

- Accessory
- Middle Size
- Mini Size
- Large Size
- Standard Size

[M Series](#) >[FLOS & FLOS+](#) >[Power](#) >[RBL](#) >[HS-Lok](#) >[NMEA 2000](#) >[Heavy Duty Shielded](#) >[RJ](#) >[USB](#) >[D-Sub](#) >[HDMI](#) >[DVI](#) >[Fiber Optic](#) >[RF](#) >[Cable Joiner](#) >[Cable Gland](#) >[Pressure Relief Vent](#) >[LED Light Guide](#) >[D-Sub](#) >

BD-06BFFA-QL8SP0

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: UL1977

You must login first for view the price


Quantity

- 1 +

Check Stock

Add to Cart

Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

X-Lok, Standard Size,...
AB-BD06ML-BDBL-...
-20°C ~ +80°C

X-Lok, Standard Size,...
AB-BD06ML-BDBL-...
-20°C ~ +80°C

X-Lok, Standard Size,...
AB-BD06ML-BDBL-...
-20°C ~ +80°C

X-Lok, Standard Size,...
AB-BD06ML-BDBL-...
-20°C ~ +80°C

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 5A	Connector Type Field Installable
Shielded Plastic, Non-shielded	No. of Contacts 06
Connector Gender Female	Backshell Straight
Mating Style Push Lock	IP Rating IPX8
Assembly Style Crimp	
More Options	

People Also Bought

