


Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- Q8**
- Accessory
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



Q8U-06BFFA-QL8001

Operating Temperature: -40°C ~ +105°C
Transmission Speed: N/A
Shielded: Plastic, Non-shielded
Jacket Material: N/A
Certificate: N/A

You must login first for view the price

Quantity - 1 + Check Stock

Add to Cart Inquiry 

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type Search



HS-Lok, Q8, Plastic, -40°C ~ +105°C

- 0 +

☐



HS-Lok, Q8, Plastic, -40°C ~ +105°C

- 0 +

☐



HS-Lok, Q8, Plastic, -40°C ~ +105°C

- 0 +

☐



HS-Lok, Q8, Plastic, -40°C ~ +105°C

- 0 +

☐



HS-Lok, Q8, Plastic, -40°C ~ +105°C

- 0 +

☐



HS-Lok, Q8, Plastic, -40°C ~ +105°C

- 0 +

☐

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current 2A	Connector Type Field Installable
Shielded Plastic, Non-shielded	No. of Contacts 06
Connector Gender Female	Backshell Straight
Mating Style Push Pull	IP Rating IP68
Assembly Style N/A	
More Options	

People Also Bought

