



with metric thread – stainless steel

Choose version

stainless steel 1.4305, uncoated with undercut

▼

 **Download information as pdf**

☐ **Show technical details**

Order number	Hexagonal size (SW)	Thread (G1/G2)	Standard lengths in mm (L	Amount	Order
241 x (length)	SW4	M2	Please select ▼	100	Please log in 
242 x	SW5	M2.5	Please select ▼	100	Please log in 
244 x	SW5.5	M3	Please select ▼	100	Please log in 
246 x	SW7	M4	12 ▼	100	Please log in 
248 x	SW8	M5	Please select ▼	100	Please log in 
249 x	SW10	M6	Please select ▼	100	Please log in 
2413 x	SW13	M8	Please select ▼	100	Please log in 

Order example: 246 × 50 = DIA / stainless steel / SW7 / M4 × 50

Minimum tensile strength: 750 N / mm²

Tolerance for length dimensions: + / - 0.1 mm

(DIN 2678-m applies for SW13)