



Representative Image

Catalog No. TC817-TB

Description: MNTG BASE .44X.44IN NAT NYL LOW-PRO

UPC No 786210826318

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Low-Profile Mounting Plate, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 11.1mm (0.437 Inches), Width of 11.1mm (0.437 Inches), Height of 4.75mm (0.187 Inches), Epoxy Glue Mounting Method

Descriptors

Category	Cable tie mounts
Special Features	These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Epoxy Glue (TC2PA)
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap
------------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	11.1 mm
Length	0.44 inch
Width	11.1 mm
Width	0.44 inch
Height	4.75 mm
Height	0.19 inch
Type of fastening	Other
Material	Plastic
Material quality	Polyamide (PA)

by ABB

ETIM	EC000449 Mounting base and -element for cable ties
Colour	Natural colour

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E16592	N/A	FKAV	N/A	N/A