






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/16/11	D.GRIFFIN
B	ECN 6627: REVISED PIN 1 POSITION	1/16/13	D.FRISIELLO



RECOMMENDED
PANEL CUTOUT



RECOMMENDED
PCB CUTOUT



NOTES:

MATERIAL:
CONTACTS: BRASS
INSULATOR: PBT, UL94V-0 RATED (WHITE)
SHELL: BRASS

FINISH:
CONTACT: 30μ INCH SELECTIVE GOLD
SHELL: NICKEL

ELECTRICAL CHARACTERISTICS:
CONTACT CURRENT RATING: 1.5 AMPERES.
DIELECTRIC WITHSTANDING VOLTAGE: AC 500V R.M.S.
INSULATION RESISTANCE: 1000 MEGOHMS MINIMUM
CONTACT RESISTANCE: 30 MILLIOHMS MAXIMUM
OPERATING TEMPERATURE: -55°C +85°C.

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

COMPONENT SHALL BE PACKAGED IN QUANTITY OF 10 PER BAG
IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 PROJECTION 	APPROVALS	DATE	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D.FRISIELLO	11/30/11		
	CHECKED BY D.PARHAM	11/30/11	CATEGORY USB	
	APPROVED BY S.SMITH	11/30/11	PRODUCT DESCRIPTION USB TYPE "B" CONNECTOR WITH FLANGE	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. UC-B-PMT	REV. B
	SCALE: NONE		CAD FILE: UC-B-PMT.SLDDRW	SHEET 1 OF 1