

Data Sheet | Item Number: 211-927

Nozzles; Length: 23 mm; For the use of 211-821; halogenated; Cable outer diameter: 14.0 ... 22.0 mm; transparent

<https://www.wago.com/211-927>



Color: ☐ transparent

Technical data

Suitable	for wire diameter 14 ... 22 mm
Delivery form	Component
Properties	for one 211-821 marker
Printing device	Smart Printer (thermal transfer printer)

Physical data

Length	23 mm
--------	-------

Mechanical data

Mounting type	Sliding on conductor
---------------	----------------------

Material data

Color	transparent
Material	Polyvinyl chloride
Adhesive information	without adhesive
Halogen-free	No
Weight	2.5 g



Environmental requirements		
Ambient temperature (storage)		+5 ... +40 °C
Ambient temperature (operation)		-15 ... +70 °C
Relative humidity		40 ... 80 %

Commercial data		
PU (SPU)		100 pcs
Packaging type		Bag
Country of origin		IT
GTIN		4055143381222
Customs tariff number		39269097900

Product Classification		
UNSPSC		39121722
eCl@ss 10.0		27-40-04-01
eCl@ss 9.0		27-40-04-01
ETIM 9.0		EC001530
ETIM 10.0		EC001530
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 211-927

↓

1 Compatible Products
1.1 Required Accessories
1.1.1 Marking
1.1.1.1 Marker



Item No.: 211-821
Marker; for Smart Printer; for use in nozzles;
Length: 23 mm; 2500 pieces on roll; white


Installation Notes

Application



Slide the marker into the marking sleeve receptacle. Replacing the marker is also possible after the conductor has been terminated.

Application



Compress the sleeve and slide it onto the conductor to be marked.