

Johanson Part Number 2450BL15B0050001E

Johanson Part Number: 2450BL15B0050001E	Johanson Company: JTI
Legacy P/N: 2450BL15B050E	Size for Capacitors (EIA): None
Description: RF Baluns, 805, 2400-2500MHz, 3W, 1, Ni/Sn (RoHS), , 7" Reel Embossed Tape	Specification Number: None
Life Cycle Stage: Active	NCNR: No
AEC Q200 Qualified: No	Thickness (Max): 0.037
Schedule B: 8534.00.00.85	Thickness (Min): 0.029
ITAR: No	End Band(Min): 0.01
ECCN: EAR99	End Band (max): 0.016
RoHS Compliance: Yes, RoHS 10/10	Standard Item: Yes
REACH: Yes	Lead Time Typical (Weeks)*: 17
Country of Origin: TW	Length (Min): 0.075
Product Family: Integrated Passive Components	Length (Max): 0.083
Product Subfamily: RF Baluns	Width (Min):0.045
Capacitance Value: None	Width (Max): 0.053
Cap Unit of Meas: None	Part Weight (mg): None
Tolerance: None	Packaged Width (lb) Arm: None
Voltage: None	Packaging: 7" Reel Embossed Tape
Dielectric Temp Coefficient: None	Packaging Qty: 4000
Termination: 0	Operating Temp Range: -40° C to +85° C
Marking: Special	Storage Temp Range (Packaged): +5° C to +40° C with RH 20% to 70%
Product Release Date: Jan. 10, 2006	Storage Temp Range (None Operating): -65° C to +125° C
Harmonization: 8534.00.00.85	

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://johansontechnology.com/baluns>

Printed from: <https://www.johansontechnology.com/part/2450BL15B0050001E/>