


Sub-bases for logic elements and relays rotatable/81 532 104 Part number 81532104


■ xxx

	Type	Description
81532104	rotatable/81 532 104	Sub-bases for logic elements and relays
81532102	rotatable/81 532 102	Sub-bases for logic elements and relays
81542002	rotatable/81 542 002	Sub-bases for logic elements and relays
81532001	Rear/81 532 001	Sub-bases for logic elements and relays
81531001	Rear/81 531 001	Sub-bases for logic elements and relays


2-hand control relay

Pressure delay sensor	■ 1
Pressure switches	■ 1
Adjustable pressure switches (manostats) and Adjustable vacuum switches (vacuostats)	■ 1
Leak sensor and amplifier relays	■ 1
Logic elements and Timers (with adjustable timing)	■ 1
Regulator accessories	■ 1
Memory element	
Miniature power valve	■ 1
The number indicates qty of logic footprints on the base	
Push-in connection for semi-rigid tubing Ø 4 (NFE 49100) mm	rotatable
Mounting	DIN rail 35 mm EN 50022
Weight (g)	56

Dimension Diagram : 81 532 104 - 81 532 102


N°	Legend
1	Sub-base supplied with inlet connection
2	Push-in connection for semi-rigid tubing Ø 4 mm (NFE 49100)
3	Mounted on Q EN 50022

: Bases for elements and relays - Front connecting 81 532 102/104



N°	Legend
1	Input port (green - port 1)
2	Output port (red - port 3)
3	Input/supply port (yellow - port 2) Ø 4
4	Input indicator (green)
5	Output indicator (red)
6	1/4 turn screws
7	Marking tag
8	Arrow indicating flow direction