

Data Sheet | Item Number: 261-361

End plate; with fixing flange; gray

<https://www.wago.com/261-361>



Color: ■ gray

Physical data		
Width		3 mm / 0.118 inches
Height		18 mm / 0.709 inches
Depth		28 mm / 1.102 inches

Material data		
Note (material data)		Information on material specifications can be found here
Color		gray
Material group		I
Insulation material (main housing)		Polyamide (PA66)
Flammability class per UL94		V0
Fire load		0.03 MJ
Weight		1.1 g

Environmental requirements		
Processing temperature		-35 ... +85 °C
Continuous operating temperature		-60 ... +105 °C

Commercial data		
Product Group		9 (Std Chassis Mt Blocks)
PU (SPU)		300 (50) pcs
Packaging type		Box
Country of origin		CH
GTIN		4017332141260
Customs tariff number		85389099990



Product Classification	
UNSPSC	39121702
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 9.0	EC000886
ETIM 10.0	EC000886
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 261-361

↓

Documentation			
Bid Text			
261-361	19.02.2019	xml 2.55 KB	↓
261-361	17.08.2017	doc 23.00 KB	↓

CAD/CAE-Data

CAD data

2D/3D Models 261-361

↓

CAE data

EPLAN Data Portal 261-361

↓

WSCAD Universe 261-361

↓

ZUKEN Portal 261-361

↓



1 Compatible Products
1.1 Optional Accessories
1.1.1 Installation
1.1.1.1 Mounting accessories



Item No.: 209-123
Mounting foot with screw; can be screwed on terminal blocks with fixing flange; 6.4 mm wide; gray