

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BA-2RV314-A22**BA-2RV314-A22**

PAGE 1 OF 1

MDRAWING
NUMBERISSUE
4

REPLACES X92105-BA

RELEASE NO. PR-18305

CHECK

REVISIONS

A	CO	77590
	SAD	
9	JUN 94	
B	CO	82886
	JALA	
23	APR 96	
C	CO	093346
	DLT	
26	AUG 98	

CHECK

25 MAY 90


JAP

CHECK

B A B 23 MAY 90

FORMTEK

FO-52850-COI



NOTE

- ① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $.139$ MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE-----4 1/2 OZ MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE-----1/2 OZ MIN	L23 20A 125, 250, OR 480 VAC	UNLESS OTHERWISE NOTED
PRETRAVEL-----.470 MAX	10A 125 VAC "L"	DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL-----.065 MAX	1 HP 125 VAC, 2 HP 250 VAC	TOLERANCES ARE:
OVERTRAVEL-----.047 MIN	1/2 A 125 VDC, 1/4 A 250 VDC	ONE PLACE (.0) $\pm .030$
	L288	TWO PLACE (.00) $\pm .015$
	L299	THREE PLACE (.000) $\pm .005$
	L308	ANGLES $\pm$
	CE D PA	WEIGHT
	20(3)A 250V $\sim$ T85 5E4	