

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)

[Home](#) / [Products](#) / [M Series](#) / [M12 \(A\)](#)

Product Line

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

M Series >

Accessory

M5

Guided M8

M8

M10.5

M12 (A)

M12 (B)

M12 (D)

M12 (I)

M12 (K)

M12 (L)

M12 (S)

M12 (T)

M12 (V)

M23

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >


Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



APPM-A05MAPAN-AS1

Operating Temperature: -20°C ~ +80°C

Transmission Speed: N/A

Shielded: Metal, Non-shielded

Jacket Material: N/A

Certificate: N/A

You must login first for view the price

Quantity

- 1 +

Check Stock

Add to Cart

Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 4A	Connector Type Field Installable
Shielded Metal, Non-shielded	No. of Contacts 05
Connector Gender Male	Backshell Straight
Mating Style Push Pull	IP Rating Non-waterproof
Assembly Style N/A	
More Options	

People Also Bought