








REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C190346	2019/03/05	Vicky	Change Note



Recommended Panel
Cut-Out




ABD-XXPMFS-LC7001
02: 2Pin
06: 6Pin




6 Pin


Pin Assignments
Front View




5 Pin



4 Pin



3 Pin



2 Pin

Pin Assignments Front View

Note:

- * (C) Important Dimension To Check.
- * Waterproof Rate: IP67, Unmated.
- * Housing: Thermoplastic, Black
- * Pin: Copper Alloy, Gold Plated.
- * Nut: Thermoplastic, Black.
- * Gasket: Rubber, Gray.
- * Use with waterproof cap or dust cap
Maximum Panel Thickness: 2.8mm
- * Use without waterproof cap or dust cap
Maximum Panel Thickness: 4.0mm
- * Gasket and Nut are packed separately
in PE bags. (Gasket/Nut不組裝, 散裝出貨)

UNIT: mm		TITLE	STANDARD PANEL LOCK M CONN F PIN
TOLERANCE		SCALE	3:2
.X ±0.25		SIZE	A4
.XX ±0.1		SHEET	1 OF 1
.XXX ±0.05		REV.	B
ANGLES ±1°		WC-REV.	A.1
		QC	Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Vicky	2019-03-05
ABD-XXPMFS-LC7001	CHECKED BY	DATE
CUSTOMER	Rita	2019-03-05
ALTW	APPROVED BY	DATE
	Max	2019-03-05