



REVISIONS			
SN	EDN	DESCRIPTION	DATE
A			08/06/07

D-SUB TECHNICAL DATA

SHELL : Steel, 2.5um (100u") min tin over 1.25um (50u") min nickel
BODY : Glass filled thermoplastic.
Flame retardant to UL94 V-0 Color Black
CONTACTS : brass.
Gold flash over 1.25um (50u") min nickel
ELECTRICAL : Voltage rating :1000 V RMS at 50 Hz
Current rating 3A.
Insulation resistance >1000 M Ohms
Contact resistance 20 mOhms max.
CLIMATIC : Temperature range -55 °C up to 125°C
MARKING : Amphenol...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 717 SD D 50 P



DIMENSIONS SPECIFIED			
TOLERANCES		APPROVAL	DATE
U.S.	METRIC	DRAWN	Iss. young 08/06/07
.X +/-	0.50	CHECKED	10k. young 08/06/07
.XX +/-	0.30		
.XXX +/-	0.20		
ANGLES +/-	2°		
FOR MATERIALS AND FINISHES			
REMOVE SHARP EDGES			
DIMENSIONS			
THICKNESS	THICKNESS	ANGLE OF PROJECTION	
METRIC	MM		
TITLE			
Stamped and Formed connector, SD series			
SIZE DRAWING NO.		REV.	
A4		A	
SCALE		SHEET 1 OF 1	
NONE			

A

B

C

D

4

3

2

1

4

3

2

1