


SOCKET PIN


Socket Pin (Small Type) [PC Series] (100pcs/pack)

- Socket pin for DIP relay, XTAL, IC, etc.
- [PK](#), [CD](#) series are available for mounting child board.
- PC-10 has Protect Shield.


Model No.	Finsih		Recommended male pin diameter (phi mm)	Depth (mm)	Bottom	Recommended through-hole diameter (phi mm)
	Contact part	Body part				
PC-23	Au plating	Sn plating	0.43 to 0.51	3.0	close	1.05
PC-4	Au p	Sn p	0.99 to 1.04	4.83	close	1.9
PC-44	Au p	Sn p	0.99 to 1.04	any	open	1.9
PC-5	Au p	Sn p	0.76 to 0.81	4.83	close	1.9
PC-55	Au p	Sn p	0.76 to 0.81	any	open	1.9
PC-6	Au p	Sn p	1.24 to 1.30	5.08	close	2.6
PC-7	Au p	Sn p	0.60 to 0.66	3.58	close	1.4
PC-8	Au p	Sn p	1.50 to 1.58	5.08	close	2.6
PC-9	Au p	Sn p	0.85 to 0.95	6.0	close	1.9
PC-10	Au p	Sn p	0.4 to 0.5	3.6	close	1.0
PC-11	Au p	Sn p	0.25 to 0.45	3.1	close	1.0
PC-20	Au p	Sn p	0.4 to 0.6	any	open	1.4




PC-23




PC-4, 5, 9




PC-44, 55




PC-6, 8




PC-7



PC-10



PC-11



PC-20

Material	Body part	Brass, Copper
	Contact part	Beryllium copper
Rated current	PC-23, 10, 11, 20	1A
	PC-4, 5, 7, 9	5A
	PC-6	10A
	PC-8	15A

Contact resistance	10m ohm or less
Mating/unmating (durability)	100 or more
Mating/unmating forces (1 pin)	30g or more