


THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.


BACKSHELL KIT INCLUDES:

- (2)BACKSHELL HALVES
- (1)GROMMET
- (2)JACKSCREWS
- (2)SHELLSCREWS
- (2)CLAMPSCREWS
- (1)METAL CLAMP
- (1)METAL CLAMP FLAT

NOTE: 9 POSITION HAS ONLY 1 JACKSCREW



BACKSHELL MATERIAL: DIE CAST ZINC ALLOY
PLATING: NICKEL PLATED
GROMMET: THERMOPLASTIC ABS
COLOR: NATURAL NICKEL PLATED
SHELLSCREWS: STEEL, ZINC PLATED
JACKSCREWS: STEEL, ZINC PLATED WITH PLASTIC KNOB
CLAMPSCREWS: STEEL, ZINC PLATED
CLAMP: STEEL, SHEET, NICKEL PLATED
OPERATING TEMP: -40°C TO +120°C



* UNLESS OTHERWISE SPECIFIED TOLERANCES
ON DECIMAL IS: ANGLE $\pm 1^\circ$
UNIT: MM .X ± 0.5

DIMENSIONS(mm/in)				
SIZE	A $\pm^{.50}_{\pm.020}$	B $\pm^{1.6}_{\pm.063}$	C $\pm^{1.6}_{\pm.063}$	D $\pm^{.50}_{\pm.020}$
9	32.0	43.0	15.5	—
	1.260	1.693	0.610	—
15	40.4	43.0	15.5	33.32
	1.591	1.693	0.610	1.312
25	54.0	48.0	15.5	47.04
	2.126	1.890	0.610	1.852
37	70.5	53.0	15.5	63.50
	2.776	2.087	0.610	2.500

ORDERING INFORMATION:

SIZE	P/N – KITTED	PRODUCT CODE
9-WAY	6560-0139-11	MHDM35-9-K
15-WAY	6560-0139-12	MHDM35-15-K
25-WAY	6560-0139-13	MHDM35-25-K
37-WAY	6560-0139-14	MHDM35-37-K

THESE DRAWINGS AND SPECIFICATIONS ARE THE
PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE BASIS FOR
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT
WRITTEN PERMISSION.

DRAWN JOHNNY		DATE 11-09-15	
APPROVED VICTOR		DATE 11-09-15	
SCALE	SHEET OF 1 OF 1	REV: 5.0	
DRAWING No MHDM35-XX-K			



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR RoHS COMPLIANCY.



MH CONNECTORS LTD.