



Drawings



Suggested Cut-out



IP	65
IK	08
Cycles	3.000.000
Operating temp.	-10° to +70°C (0° to +50°C with TI)
Storage temp.	-25° to +85°C (-25° to +55°C with TI)

Marking
Chemical engraving + color filling



Tolerances:			Date	Name	YME IP 16 N		
			05/12	dr			
IP rating	05/19	dr	knitter-switch			30 26 42	
Rename	02/14	dr					
Rename	11/13	dr					
Modifications	Date	Name					
						Page	
						1/1	