


UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES: .010 DECIMALS; .004 ANGLES $\pm$.30°.
2. LOCATION: CONCENTRICITY OF ANY DIAMETERS MAY NOT EXCEED THE SUM OF THEIR TOLERANCES.
3. REMOVE ALL BURRS, BREAK SHARP EDGES .003 MAX.
4. NO HOLETS PERMITTED.
5. SURFACE ROUGHNESS AS MICROINCHES RMS MAX.
6. ALL DIMENSIONS PRIOR TO PLATING.

7	1	BNC CONTACT ASSEMBLY		
8	1	HEX NUT	708-4-MOG	
9	1	LOCK WASHER	C-71-09-2-MOG	
2	1	INSULATOR		
1	1	BODY		
ITEM	REQ'D	DESCRIPTION		DWG. NO.

REVISIONS	
ISSUE	CHANGES
0	ER 9072 C.C. 7 DEC 70
1	CN 12975 A H 28 JUL 73
2	CN 14568 C GA 24 JUN 75
3	CN 19256 C GMF 7 FEB 80
4	CN 21551 C KOR 21 JAN 81
S-D	
REF.	
FINISH	
SPEC KER-10004	
MATL	
SPEC	
BMC BULK HEAD RECEPTACLE	
DRAWN C.C.	DATE 3 DEC 70
APPR. <i>CC</i>	DATE 12-7-70
KINGS ELECTRONICS 48 MARLBOROUGH ROAD. TUCKAHOE, N. Y.	
AC-79-131	