

Rack Mount Basic PDU 1589-RF-RR Series

20A | Single-Phase 125V | Front or Rear Facing 5-15/5-20R Outlets

Features

- Designed for power distribution from the front or rear of the unit.
- 1U horizontal 19" rackmount installation.
- Available with an on/off switch or red pilot light to indicate power on.



Specifications

- Heavy duty 12 gauge wire cord - 12/3 SJT type for extreme temperature ranges and integral molded plug.
- Heavy-duty black receptacles rated for 20A, 125VAC service (NEMA 5-20R, Single T-Slot supports 5-15/5-20 devices).
- Plug types available are NEMA 5-20P straight blade or NEMA L5-20P locking type.
- Includes 20 Amp, 125 VAC circuit breaker to prevent accidental overload.
- The operating temperature is from -20 degrees C to +60 degrees C.
- UL/cUL recognized Standard UL1363 and CSA C22.2 No. 308-14.
- Finished in textured RAL9005 black powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America.



Metered Specifications

- Unit includes - easy to read 0.37" high, red LED ammeter (1.38" x 0.88" display).
- Digital ammeter accuracy +/- 0.1 Amps.

Shielded Cord Specifications

- Shielded cord reduces EMI/ RFI and "dirty" power from utilities.
- Shielding is by way of 100% coverage in aluminum mylar foil with a 20 gauge drain wire.

Plug types



5-15P Straight Blade



L5-15P Locking
Type

Accessories

- Hardware for Rack Mounting Solutions

- Rack Rail Depth Adapter Kit 4 Inch Rack Equipment Offset Bracket

On/Off Switch	Illuminated Power Indicator	Overall Dimensions			Number of		NEMA Type		Cord Length	Plug			
		Height	Width	Depth	Outlets		Outlet	Plug		Blade Type	Amp Metered	Surge Protected	Shielded Cord
					Front	Rear							
Part No.	Part No.												
1589H6C1B KRF	1589T6C1B KRF	1.72	19.00	2.66	6	0	5-20R	L5-20P	6 ft	Locking	No	No	No
1589H6D1B KRF	1589T6D1B KRF	1.72	19.00	2.66	6	0	5-20R	L5-20P	15 ft	Locking	No	No	No
1589H6F1B KRF	1589T6F1B KRF	1.72	19.00	2.66	6	0	5-20R	5-20P	6 ft	Straight	No	No	No
1589H6F1B KRFAM	1589T6F1B KRFAM	1.72	19.00	2.66	6	0	5-20R	5-20P	6 ft	Straight	Yes	No	No
1589H6G1B KRF	1589T6G1B KRF	1.72	19.00	2.66	6	0	5-20R	5-20P	15 ft	Straight	No	No	No
1589H8C1B KRF	1589T8C1B KRF	1.72	19.00	2.66	8	0	5-20R	L5-20P	6 ft	Locking	No	No	No
1589H8D1B KRF	1589T8D1B KRF	1.72	19.00	2.66	8	0	5-20R	L5-20P	15 ft	Locking	No	No	No
1589H8F1B KRF	1589T8F1B KRF	1.72	19.00	2.66	8	0	5-20R	5-20P	6 ft	Straight	No	No	No
1589H8G1B KRF	1589T8G1B KRF	1.72	19.00	2.66	8	0	5-20R	5-20P	15 ft	Straight	No	No	No
1589H6C1B KRR	1589T6C1B KRR	1.72	19.00	2.66	0	6	5-20R	L5-20P	6 ft	Locking	No	No	No
1589H6C1B KRRAM	1589T6C1B KRRAM	1.72	19.00	2.66	0	6	5-20R	L5-20P	6 ft	Locking	Yes	No	No
1589H6D1B KRR	1589T6D1B KRR	1.72	19.00	2.66	0	6	5-20R	L5-20P	15 ft	Locking	No	No	No
1589H6F1B KRR	1589T6F1B KRR	1.72	19.00	2.66	0	6	5-20R	5-20P	6 ft	Straight	No	No	No
1589H6F1B KRRAM	1589T6F1B KRRAM	1.72	19.00	2.66	0	6	5-20R	5-20P	6 ft	Straight	Yes	No	No
1589H6G1B KRR	1589T6G1B KRR	1.72	19.00	2.66	0	6	5-20R	5-20P	15 ft	Straight	No	No	No
	1589T8C1B KRR	1.72	19.00	2.66	0	8	5-20R	L5-20P	6 ft	Locking	No	No	No
1589H8D1B KRR	1589T8D1B KRR	1.72	19.00	2.66	0	8	5-20R	L5-20P	15 ft	Locking	No	No	No
1589H8D1B KRRV		1.72	19.00	2.66	0	8	5-20R	L5-20P	15 ft	Locking	No	No	Yes
1589H8F1B KRR	1589T8F1B KRR	1.72	19.00	2.66	0	8	5-20R	5-20P	6 ft	Straight	No	No	No
1589H8G1B KRR	1589T8G1B KRR	1.72	19.00	2.66	0	8	5-20R	5-20P	15 ft	Straight	No	No	No
1589H8G1B KRRV		1.72	19.00	2.66	0	8	5-20R	5-20P	15 ft	Straight	No	No	Yes
1589H12F1 BKX	1589T12F1B KX	1.72	19.00	2.66	6	6	5-20R	5-20P	6 ft	Straight	No	No	No
1589H12G1 BKX	1589T12G1 BKX	1.72	19.00	2.66	6	6	5-20R	5-20P	15 ft	Straight	No	No	No

Tags: **1U Rack-Mount Power Strip**

Data subject to change without notice.

© 2026. Hammond Manufacturing Ltd. All rights reserved.