

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ - 2RT**BZ-2RT**

PAGE 1 OF 1

MDRAWING
NUMBER

13

ISSUE

REVISIONS

A	CO17410
B	C H
	22 APRIL 63
B	CO26678
	R E R
	1 DEC 69
C	CO-
	59351-D
	JWB
	18 JUL 91
D	CO-
	77589
	K O R
	29 MAR 94
E	CO93346
	DLT
	4 SEP 98

REPLACES

RELEASE NO.

CHECK

CHECK

14 JUN 63

L.S.D


CHECK

G C H 22 APRIL 63

FORMTEK

FO-50378

DRAWN

6-32 UNC X .218 REF BINDER
HEAD TERMINAL SCREW AND
LOCKWASHER (SEMS) (3)

NOTE

△ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ----- 9-13 OZ
RELEASE FORCE ----- 4 OZ MIN
DIFFERENTIAL TRAVEL ----- .0004 - .0020
OVERTRAVEL ----- .005 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T

UNDERWRITERS' LAB. INC. LISTED RATING
-L96- 15 A-125, 250, OR 480 VAC
1/2 A-125 VDC, 1/4 A-250 VDC
1/8 HP-125 VAC, 1/4 HP-250 VAC
-L288- CE D SP
-L299- 16A 250V ~ T85 5E4
-L306-

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT .065 LB MAX