


- BACKSHELL KIT INCLUDES:**
- (2) BACKSHELL HALVES
 - (2) 4-40 THUMBSCREWS
 - (2) HOUSING SCREWS/NUTS
 - (1) SET OF COMPRESSION INSERTS-VARIOUS SIZES
- DIAMETERS:** 4mm (.157"), 5mm (.197"), 7mm (.276") , 9mm (.354")



DIMENSIONS (mm/in)				
SIZE	A ^{±.25} _{±.010}	B ^{±.13} _{±.005}	C ^{±.25} _{±.010}	D ^{±.25} _{±.010}
9	31.20	24.99	39.90	15.00
	1.228	0.984	1.571	0.590
15	39.50	33.32	41.50	15.00
	1.555	1.312	1.634	0.590
25	53.40	47.04	48.60	15.00
	2.102	1.852	1.913	0.590
37	69.70	63.50	53.60	15.00
	2.744	2.500	2.110	0.590

ORDERING INFORMATION:

SIZE:	P/N - KITTED:	PRODUCT CODE:
9-WAY	6560-0108-01	MHDTPPK-9-K
15-WAY	6560-0108-02	MHDTPPK-15-K
25-WAY	6560-0108-03	MHDTPPK-25-K
37-WAY	6560-0108-04	MHDTPPK-37-K

SIZE:	P/N - BULK:	PRODUCT CODE:
9-WAY	6561-0108-01	MHDTPPK-9
15-WAY	6561-0108-02	MHDTPPK-15
25-WAY	6561-0108-03	MHDTPPK-25
37-WAY	6561-0108-04	MHDTPPK-37

PLASTIC: ABS POLYLAC - BLACK - UL RECOGNIZED
JACKSCREWS: STEEL - BLACK OXIDE
M3 HOODSCREWS: STEEL - BLACK OXIDE
COMPRESSION INSERT: ABS UL RECOGNIZED
M3 NUT: STEEL - BLACK OXIDE
OPERATING TEMP: - 55°C TO + 110°C

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN	DATE
		P. JENKINS	03-14-12
		APPROVED	DATE
D. CROFT			03-14-12

MH CONNECTORS LTD.

ROHS COMPLIANT



SCALE	SHEET	OF	REV.
NTS	1	1	A
DRAWING No			
MHDTPPK-SERIES			