



HAHN - Elektrobau GmbH & Co. KG


Bellersheimerstraße 45
35410 Hungen
Germany

phone: +49 (0) 6402/808-0
fax: +49 (0) 6402/808-60
email: info@hahn-trafo.de




Data sheet: BV EI 302 2007

Size 2 a: height 21.8 mm	1,8 VA	ta 40/F	BV EI 302 ...
--------------------------	--------	---------	---------------

Several hundreds of typen provide high electrical safety and long service-life for printed circuit boards, household appliances, leisure electronics, heating and control technology as well as in assembly techniques. Transformers for special requirements with lower open-circuit (no-load) loss capacity are also available in the range.

absolutely short-circuit-proof minimal size test certifications to ENEC 10-, VDE, UL- and CSA-regulations vaccum encapsulated, bobbin with dual chamber windings temperature class ta 40°C/F and ta 70°C/F high electrical safety and long service-life properties individually tested with certificate excellent temperature fluctuation resistance properties self-extinguishing cast housing and sealing material	
---	---

Article no. BV	Output ta 40°C/F	prim.V	Connecting pins	Operating point sec. $\pm 5\%$	Connecting pins	No-load voltage V $\pm 5\%$
BV EI 302 2007	1,8	230	1-5	2x12 V 75 mA	6-7/9-10	17,8/17,8



Maße ohne Toleranzangabe $\pm 0,3$ mm,
Ausführungsänderungen vorbehalten

Dimensions with no indication of tolerances $\pm 0,3$ mm.