






SUGGESTED PCB LAYOUT (TOL:±0.05)
COMPONENT SIDE VIEW




SUGGESTED PANEL CUTOUT



CONNECTOR ASSEMBLED
TO PANEL AND PCB


4G62 GIGABIT CIRCUIT




C1-C2 = 0.1uF 50V, CAPACITOR
C3 = 1000pF 2KV, CAPACITOR
R1-R4 = 75 ohms, 1/16W, RESISTOR
R5 = 1M ohms, 1/10W, RESISTOR
R5 = 22M ohms, 1/16W, RESISTOR, ONLY
FOR 3-1840437-1, 3-1840437-9

LED OPTION


OPTION 1



OPTION 2



OPTION 3



THIS DRAWING IS A CONTROLLED DOCUMENT. AND COMPLIANT TO ASME Y14.5M		DWN TOMMY REN 10AUG2007	 a bel group		DONGGUAN CHINA
DIMENSIONS: mm		CHK KEITH ZHU 10AUG2007			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD TEDDY XIONG 10AUG2007			
0 PLC ± 1 PLC ±0.25 2 PLC ±0.25 3 PLC ±0.25 4 PLC ± ANGLES ± APPLICATION SPEC		MODEL NAME MAGJACK SINGLE NON-POE			
PRODUCT SPEC 108-2207		DESC 1X1 4G62 GIGABIT TAB DOWN LOW PROFILE OFFSET W/ LED		SIZE A2	CAGE CODE C-1840437
		DRAWING NO C-1840437		RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE 4:1	SHEET 2 OF 2
				REV K	