


Inductor

TCK-145





Order Code	TCK-145
Inductance	6.8 µH ±20% (at 1 kHz / 1 V)
Impedance (DCR)	300 mΩ max.
Rated Current	1 A max.
Operating Temperature	-40°C to +125°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-145



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	3.1 ±0.5
B	3.5 ±0.5
C	2.1 ±0.5
D	1.2 typ.
E	3.6
F	1.7
G	0.8

All specifications valid at +25°C, unless otherwise stated.