



Part Number : 638257700

Series Number : 207129

Product Category : Crimp Presses and Crimp Hand Tools

Product Description : Hand Crimp Tool for 2.28mm (.090") Sealed Receptacle Terminal

Status : Active

Documents & Resources

Tooling Specifications
[Application Tooling Specification ATS-6382577HM-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for 2.28mm (.090") Sealed Receptacle Terminal
Comments	Die sets are not sold separately; the complete hand tool needs to be ordered to obtain the die set; Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Family	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	887191247762
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

This document was generated on Jul 30, 2024