








PCB LAYOUT (CONNECTOR TOP VIEW)


- RJ45 CONTACTS
- RJ45 SHELL GROUND CONTACT
- CONNECTOR LOCATION PINS



PANEL CUT OUT



1.2-2.5mm RECOMMEND
PANEL THICKNESS



RJXS8FP5HP

SERIES PREFIX
CONTACT LAYOUT (RJ45 STYLE)
GENDER
FOUR HOLE RECEPTACLE HOUSING IP65, WITH CAP (BLACK)
TRANSMISSION CLASS (CAT5e)
HORIZONTAL MOUNT (PCB THRU HOLE)
POTTED

RECOMMEND MINIMUM MOUNTING PITCH



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE:		THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER		Amphenol Amphenol Australia Pty.Ltd, 22 Industry Blvd Carrum Downs, VIC 3201	
LINEAR	ANGULAR	MATERIAL:	DRN: J.W	DATE: 28/08/2023	TITLE: XLNnet, HORZ, IP65, POTTED, UNSHIELDED, W/CAP, PANEL THICKNESS 1.2-2.5
X ±10 X.X ±5 X.XX ±1	X" ±1 X"X" ±30' X"XX" ±15'	SEE COMPONENTS	CKD: P.M.	DATE: 28/08/2023	PART No: RJXS8FP5HP
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS		FINISH: SEE COMPONENTS	APP'D: P.M.	DATE: 28/08/2023	SHEET 1
DO NOT SCALE		DIMENSIONS IN MILLIMETRES	SCALE: NTS	SIZE: A3	DRAWING No. 55011417-100-1
		THIRD ANGLE PROJECTION			SHEET 2/3