

[Home](#) / [Products](#) / [Electrical & Electronic](#) / [Wiring Devices](#) / [Locking Devices](#) / [Insulgrip Twist-Lock](#) / [HBL2411](#)

HBL2411

by Hubbell Wiring Device-Kellems
Catalog ID: HBL2411

Locking Devices, Twist-Lock®, Industrial, Male Insulgrip® Plug, 20A 125/250V AC, 3- Pole 4-Wire Grounding, NEMA L14-20P, Screw Terminal, Black and White Nylon.

- Superior cord grip design protects terminations from excess strain.
- Clear, funnel shaped wire entry for ease of termination.
- Integral dust shield protects wiring chamber from dust or contaminants.

Standard Product



Where to Buy

Search Location

WHERE TO BUY

Add to Project List

Contact Us

Product Details

Resources / Downloads

Product Details

General

Application	Extra Heavy Duty Industrial
Color	Black, White
Cord Range	0.350"-1.150" (9-29)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2 (1)
Item Type	20A Male Insulgrip® Plug
Material	Nylon

Number Of Poles	3 Poles
View All	

Resources/Downloads

Specifications

 [Wiring HBL2411 Specification Sheet](#)

Catalog Page

 [Wiring B-22 Catalog Page](#)

Literature

-  [Download All](#)
-  [Entertainment Product Solution Guide](#)
-  [Insulgrip® Straight Blade and Twist-Lock® Devices](#)

Installation/Instruction Manual (IOM)

 [WIRING_PD1730_INSTALLINST](#)

Sales Drawings

 [WDK_HBL2411_DRAWINGS_PDF](#)

Engineering Drawing

 [HBL2411 AutoCAD Drawing](#)

Related Products



HBL2416



HBL2410



SK3



HBL2410RT



CUSTOMER SUPPORT

[Contact Us](#)

OUR COMPANY

- [About Us](#)
- [Our Brands](#)
- [Press Releases](#)
- [Careers](#)
- [Investors](#)

GET IN TOUCH

Hubbell Incorporated
40 Waterview Drive
Shelton, Connecticut
USA 06484-1000













