

Data Sheet | Item Number: 249-558

WSB marking card; as card; MARKED; 100,103,...187 &101,...188 & 102...189; not stretchable; Horizontal marking; snap-on type; white

<https://www.wago.com/249-558>



Color: white

Similar to illustration

Technical data		
Marking method	Thermal transfer	
Marking	100, 103, 106, ..., 187 and 101, 104, 107, ..., 188 and 102, 105, 108, ..., 189 and 190, 193, 196, 191, 194, 197, 192, 195, 198, ;	
Marking (number)	1	
Marking direction	Horizontal marking	
Marking color	black	
Marking type	Numbers	
Marking layout	Consecutive numbers per strip	
Delivery form	Marker card	
Delivery form configuration	10 strips with 10 markers per card	
Flammability class per UL94	V2	

Physical data		
Height	152 mm / 5.984 inches	
Width	46.4 mm / 1.827 inches	
Depth	3 mm / 0.118 inches	
Marker/strip width	5 mm	
Marker width	5 mm	



Mechanical data	
Smear resistance	EN 60998-1:2004

Material data	
Color	white
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	7.8 g
Fire load	0.234 MJ

Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	50 (5) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332283595
Customs tariff number	49119900000

Product Classification	
UNSPSC	55121718
eCl@ss 10.0	27-14-11-37
eCl@ss 9.0	27-14-11-37
ETIM 9.0	EC000761
ETIM 10.0	EC000761
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 249-558	