



Power supply terminal for surface mounting (For M3, M4)

PV-3, PV-4 series

- This is used for supplying power to a surface mounting board.
- Please fit a crimping terminal (for M3) at the edge of electric wire and tighten it with a M3 screw. (PV-3)
- Please fit a crimping terminal (for M4) at the edge of electric wire and tighten it with a M4 screw. (PV-4)
- Material: Brass (PV-3), Copper (PV-4)
- Finish: Tin plating over nickel base
- Rated current: 20A (PV-3)
30A (PV-4)




■ Example of usage




■ Part No.

Part No.	Package
PV-3	Bulk (100pcs/pack)
PV-3-T	Reel (800pcs/reel)
PV-4	Bulk (100pcs/pack)
PV-4-T	Reel (450pcs/reel)



■ Recommended land information



■ Recommended metal mask thickness


150 μ m to 200 μ m

■ Tightening torque

3kgf-cm (29.4N-cm) or less (PV-3)


5kgf-cm (49N-cm) or less (PV-4)

● Taping product



- Please remove the adsorption cap after reflow.
(Adsorption cap is not included for bulk products.)

■ Dimension of PV-3-T Dimension of PV-4-T



	A	B	C	D	E	F
PV-3-T	12	7.3	6.5	7.5	16	17.5
PV-4-T	16	10.3	8.5	11.5	25	25.5