

PRODUCT TOP

CATEGORY

SPECIFICATIONS

INDUSTRIES

SERIES NAME

Enter Keyword, Product name or HRS code.

SEARCH

Product Top > LF series > LF07WBR-6P



RoHS2

[▶ Product Numbers by Series](#)[▶ Part Number Configuration](#)

LF07WBR-6P

Product	LF07WBR-6P
Series	LF
Connector Type	Receptacle
Rated Current	2 A
Rated Voltage (AC)	AC 30 V
Rated Voltage (DC)	DC 42 V

Detailed Specifications

Last Updated On Oct. 30, 2017

▼ Product information	
Part No.	LF07WBR-6P
CL No.	CL0136-1001-7-00
▼ Basic information	
Connector Type	Receptacle
Rated Current	2 A
Rated Voltage (AC)	AC 30 V
Rated Voltage (DC)	DC 42 V
Number of Positions	6
Operating Temperature	-25 to 85 °C
Water Resistance	IP 68
Withstanding voltage	300 V Max.
Locking Style	Bayonet
Wire Termination Method	Soldering
Mating/Unmating Cycles	1000
Finger Protection	No
Metal Shields	Yes

Download

 DRAWING(2D) DRAWING(3D)[▶ more](#)

ADD TO MY LIST



CONTACT US

Browsing History

**Series:** [LF](#)**Product:** [LF07WBR-6P](#)

Contact Plating	Gold
Salt Spray Test Duration (Corrosion Resistance)	48 h
Shell Material	Metal
▸ Mechanical Specifications	
▸ Dimensional Information	
▸ Packaging Specifications	

Download

Catalog	Product Series Catalog	 DOWNLOAD
Data Sheet	Drawing (2D)	 DOWNLOAD
	3D Model (IGES)	 DOWNLOAD
	3D Model (STEP)	 DOWNLOAD
	Specification Sheet	 DOWNLOAD

*I [need help](#) with a product or information

[Product Top](#)

[About Us](#)

[Specifications](#)

[Industry](#)

[Series Name](#)

[Partners](#)

[Global Site](#)

[Privacy Policy](#)

[Terms of use](#)

[Membership Agreement](#)



© 1999-2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

SUPPORT

[FAQ](#)

[CONTACT US](#)

