




606 SERIES 6mm Panel Mount Indicators

MECHANICAL / SPECIFICATIONS

MOUNTING HOLE SIZE:

0.244" (6.2 mm)

MAX PANEL THICKNESS:

0.138" (3.5 mm)

MOUNTING TORQUE:

0.362 lbs/ft (5 kg/cm) torque

VOLTAGE OPTIONS:

2, 3, 6 and 12 V DC

SINGLE-COLOR: Resistor Required

BI-COLOR: No Resistor Required

OPERATING TEMP:

-25 °C to +85 °C (-13 °F to +185 °F)

STORAGE TEMP:

-25 °C to +100 °C (-13 °F to +212 °F)

ELECTRICAL CONNECTION:

Through hole and 26AWG wire leads (bi-color only)

HOUSING:

Brass–Chrome Plated

TERMINALS:

Copper–Nickel Plated

WIRE LEADS:

6" on bi-color only

LOCK WASHER:

Iron–Nickel Plated

NUT:

Brass–Nickel Plated

CERTIFICATIONS & RATINGS

RoHS compliant

APPLICATION

The 606 Series LED Panel Mount Indicators are designed for a variety of applications such as:

- Main power indication
- Remote power indication
- Status indication
- Maintenance and warning indication
- Instrumentation

DIMENSIONS inches [mm]

FIGURE 1






FIGURE 2



DIMENSIONS (Cont'd) inches [mm]



ORDERING INFORMATION

ESD Footnote Codes: Part Number Guide All HBM Values

Part Number	Class	Color	Voltage (VDC)	Current (mA)	Typical Intensity* (mcd)	LED Position	Finish	Figure
606-1111-110F	1C	● Red	2	5	45	Protruding	Chrome	1
606-1211-110F	1C	● Green	3	15	70			
606-1311-110F	1C	● Yellow	2		60			
606-1215-110F	1C	● Green	3		70			1 with wire leads
606-1415-110F	1C	● ● Red/Green	3	10	1200/4000	Protruding Diffused		2
606-1415-120F			6					
606-1415-130F			12					
606-1415-210F	1C		2		100/400			
606-1415-220F			6					
606-1415-230F			12					
606-2111-110F	1C	● Red	2	5	45	Recess		3
606-2211-110F	1C	● Green	3	15	70			
606-2311-110F	1C	● Yellow	2		60			
606-2415-110F	1C	● ● Red/Green	3	10	1200/4000			Protruding Diffused
606-2415-120F			6					
606-2415-130F			12					
606-2415-210F	1C		2		100/400	Recessed Diffused		
606-2415-220F			6					
606-2415-230F			12					

*Bi-color intensity (Red/Green)
Single-color: Resistor required
Bi-color: No resistor required



Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com

Warranty Statement: Except for the warranty expressly provided for at: www.dialight.com/resources/warranties/, Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.