

432EP6

Industrial Plug

2CMA101995R1000



Industrial Plugs, 3P+N+E, IP44, 32 A, 346 ... 415 V

GENERAL

Product Name	Industrial Plug
Product ID	2CMA101995R1000
Function	Plug
EAN	73926919958
Catalog Description	Industrial Plugs, 3P+N+E, 32 A, 346 ... 415 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420080
E-Number Norway	1540715
E-Number Sweden	E2416178
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EP
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	32 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...6 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	79 millimetre
Product Net Height	88 millimetre
Product Net Length	167 millimetre
Product Net Depth	167 millimetre
Product Net Weight	0.24 kilogram

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	2.4 kilogram
Package Length	182 millimetre
Package Units	box 10 piece