

SATO PARTS CO.,LTD. > Product Category > LED bracket / Neon bracket > Neon bracket


Product mass

Precautions for use

General notes

BN-5701

made in JAPAN



2012-06-01

Notice of partial product changes. PDF

See other change notifications

Order model number

Order model number

BN-5701-[Voltage]-[Lens color]

Order example

BN-5701-1-R (An example of ordering with a red lens with a voltage of AC100-125V.)

BN-5701-2-R (An example of ordering with a red lens with a voltage of AC200-250V.)

Basic information

Dimension

Soldering heat resistance conditions

Download

Lens color



Add to My List >

Sample request (Only available in Japan) >

*The lighting color of the lens color C is orange.

Basic information

Rating	AC100V~125V、AC200V~250V
Insulation resistance	DC500V、100MΩ Min
Withstand voltage	AC1500V (1minute)
Life	20000 hours Min (Serial lighting)
Body material	Polycarbonate
How to mount	With nut
Main insulator	PBT (UL94V-0)
Terminal type	Soldering
Lens color	R (Red)、G (Green)、OR (Orange)、C (Clear)
Panel thickness	5.0mm (MAX)
Nut torque	0.7N・m
Caution	1.When soldering, please solder with the lug facing down or horizontal.

List of partial product change notifications

2012-06-01	Notice of partial product changes. PDF
2010-03-25	Notice of partial product changes. PDF

Related products

BN-60

BN-60

Add to My List

BN-5665

BN-5665

Add to My List

BN-5668

BN-5668

Add to My List

BN-35

BN-35

Add to My List