

MICRO SWITCHFREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BA-2RV22-D6**BA-2RV22-D6**

PAGE 1 OF 1

REPLACES

PR-3096

RELEASE NO.

DRAWING
NUMBER

8

ISSUE

REVISIONS

A	PR-3096	18 SEP 69
B	CO-70184-6	18 SEP 69
C	CO-72397	18 SEP 69
D	CO-752048	18 SEP 69
E	CO-77590	18 SEP 69
F	CO-80938	18 SEP 69
G	CO-93346	18 SEP 69
H	DLT-26 AUG 98	18 SEP 69

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

FORMTEK


FO-50378-1A

DRAWN

CHECK

CHECK

CHECK

**NOTE**

△ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — 6 OZ MAX
RELEASE FORCE — — — 1 1/2 OZ MIN
PRETRAVEL — — — .250 MAX
DIFFERENTIAL TRAVEL — — .045 MAX
OVERTRAVEL — — — .030 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T
-L23- UNDERWRITERS' LAB. INC. LISTED RATING
20 A-125, 250, OR 480 VAC
10 A-125 VAC "L"
1 HP-125 VAC; 2 HP-250 VAC
1/2 A-125 VDC; 1/4 A-250 VDC
-L288-
-L299-
-L308-
CE ® ®
20(3)A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT